

WORKS AT ANY ANGLE OR POSITION

upside down,
on its side or
straight up
and down.



HIGH QUALITY MATERIALS

Manufactured from strong, non-corrosive
UV stabilised materials for a long life.

- Body - High Quality Glass Fibre Reinforced Nylon
- Diaphragms - Durable Long Life Nitrile Rubber
- Spring - High Grade Stainless Steel

INTERCHANGABLE PARTS

Diaphragm and spring
are interchangeable
with the same size
Hansen Check Valve



POTABLE WATER APPROVED

Materials approved
for use with Potable
(drinkable) Water

AS/NZS 4020



MAXIMUM WORKING PRESSURE


16 Bar (232 psi) @ 20°C

SELF CLEANING

The unique design provides
self cleaning as part of the
valve operation



Valve Open



Valve Closed

FAST RESPONSE

Smooth Operating Valve
for High Efficiency

Available in Sizes 25mm, 32mm,
40mm, 50mm, 63mm BSPT
(1", 1 1/4", 1 1/2", 2", 2 1/2" BSPT)

FOOT VALVE SOCK


An accessory that helps filter and
stop particles entering the Valve. It
also discourages the build up
of some menacing
forms of marine life.



All Hansen Foot Valves are
rigorously hand tested.

FAST AND EASY TO INSTALL

A few simple steps and you're
up and running with
your new Hansen
Foot Valve!



*We recommend
Loctite 5331.

EASY IN-LINE SERVICING

Easy access Screw Cap
provides in-line servicing for
all moving parts.



2. Your Hansen Foot Valve comes
ready to install. Connect it directly
to end of a threaded pipe, or use a
Hansen Male Straight or Reducing
Straight Coupling to connect to
your pipe. Use thread sealant
or thread tape on all threaded
connections.*

1. Visit our website to help
determine which sized
Foot Valve to use;
<http://www.hansenproducts.com/products/valve/FV-flow.htm>

HANSEN

Foot Valves

High Performance, Cost Effective Foot Valve

www.hansenproducts.com